

[See all 18 Products in Family](#)

## 10mW, 473nm DPSS Pointing Laser



DPSS Pointing Lasers

Stock **#19-469** [CONTACT US](#)

MRP ₹1,26,909

**!** Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-9	₹1,26,909 each
Qty 10+	₹1,14,271 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads



### General

**Note:**  
Compatible TEC Controller ([#19-476](#)) sold separately

**Laser Class - CDRH:**  
IIIb

### Physical & Mechanical Properties

**Length (mm):**  
100.00

## Optical Properties

TEM <sub>00</sub>	<b>Spatial Mode:</b>
473.00 ±1	<b>Wavelength (nm):</b>
1.5 Typical	<b>Beam Diameter (mm):</b>
<1.5 Typical	<b>Beam Divergence (mrad):</b>
Blue	<b>Color:</b>

## Electrical

10	<b>Output Power (mW):</b>
Not Modulated	<b>Modulation Frequency (kHz):</b>

## Hardware & Interface Connectivity

3	<b>Operating Voltage (V):</b>
<b>Power Supply:</b> Power Supply Required and Sold Separately. USA: <a href="#">#19-475</a> Europe: <a href="#">#19-475</a> Japan: Not Available Korea: Not Available China: <a href="#">#19-475</a>	

## Environmental & Durability Factors

23 to 27	<b>Operating Temperature (°C):</b>
----------	------------------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 233:</b>
China	<b>Country of Origin:</b>
<b>Imported By:</b> Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

## Product Details

- TTL Modulation up to 10kHz
- Transverse Mode TEM<sub>00</sub>
- Blue, Green, Yellow, and IR Output Wavelengths
- TEC or Heatsink Required for Operation ([Sold Separately](#))

DPSS Pointing Lasers are diode pumped solid state lasers available in output powers ranging from 1 to 100mW. With their solid state design, these lasers offer excellent mode purity and low divergence, making them ideal for applications that require long projection distances. The turnkey design featuring integrated optics and electronics in a single package is suitable for a variety of plug and play operations. DPSS Pointing Lasers provide high brightness circular output beams and are ideal for many different OEM applications. TEC Controller or heatsink is required to maintain 23°C – 27°C operating temperature range.

**Note:** Power supplies, TEC Controller ([#19-476](#)), Line Projection Heads (for 532nm - [#37-093](#))(for 1064nm - [#37-097](#)), and mounting brackets ([#37-144](#)) are sold separately.