

TECHSPEC® 1.0X - 3.0X VariMagTL™ Telecentric Lens



1.0X - 3.0X VariMagTL™ Telecentric Lens, #88-387

Stock **#88-387** 10 TO 12 DAYS

⊖ 1 ⊕

₹140,592.00

ADD TO CART

Qty 1+
₹140,592.00
Volume Pricing
Request Quote

Get Product Downloads

Filter Thread:
M30.5 x0.50 (Female)

Maximum Diameter (mm):
48.0

Resolution:
75 lp/mm @>20%

Weight (g):
296

Note:
Includes adapter to switch from 1.0X - 2.0X to 2.0X -

3.0X
Typical Telecentricity @ 588nm (°): <0.1
Typical Distortion @ 588nm (%): <0.1
Type: Telecentric Lens
Primary Magnification PMAG: 1.0X - 3.0X
Maximum Sensor Format: 2/3"
Working Distance (mm): 50.3 - 71.6
Mount: C-Mount
Style: Telecentric, Variable Magnification
Aperture (f/#): f/6 - Closed
FOV @ Max Sensor Format, H x V (mm): 8.8 x 6.6 - 2.9 x 2.2
Maximum Length (mm): 154
Minimum Length (mm): 90
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View