

10X EO HR Infinity Corrected Objective



10XEO HR Infinity Corrected Objective (#58-372)

Stock **#58-372** [CONTACT US](#)

- 1 +

₹230,202.00

ADD TO CART

Qty 1-4
₹230,202.00
Qty 5+
₹218,718.00
Volume Pricing
Request Quote

Get Product Downloads

Horizontal Field of View, 1/2" Sensor:
0.64mm

Horizontal Field of View, 2/3" Sensor:
0.88mm

Field Stop Diameter (mm):
11.00

Focal Length FL (mm):

20.00
Model Number: 28-20-45-000
Length excluding Threads (mm): 76.00
Magnification: 10X
Maximum Diameter (mm): 34
Numerical Aperture NA: 0.45
Mounting Threads: M26 x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 0.74
Depth of Field (µm): 2.70
Operating Temperature (°C): +23 ±5
Operating Humidity: 30 - 70%
Working Distance (mm): 19.00
Weight (g): 205.00
Wavelength Range (nm): 400 - 700
Style: Infinity Corrected
Parfocal Length (mm): 95
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant