

10X Mitutoyo Plan UV Infinity Corrected Objective

See More by [Mitutoyo](#)



Mitutoyo NIR, NUV, and UV Infinity Corrected Objectives

Stock **#86-175** [CONTACT US](#)

- 1 + **₹1,131,000.00**

ADD TO CART

Qty 1+
₹1,131,000.00

Volume Pricing
Request Quote

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Design Wavelength DWL (nm):
266, 355, 532

Horizontal Field of View, 1/2" Sensor:
0.64

Horizontal Field of View, 2/3" Sensor:
0.88mm

Focal Length FL (mm):

20.00
Model Number: 378-844-15
Length excluding Threads (mm): 75.00
Magnification: 10X
Maximum Diameter (mm): 34
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.25
Mounting Threads: M26 x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 1.1
Depth of Field (µm): 4.40
Field of View, 24 Diameter Field Eyepiece (mm): 2.4
Field of View, 18 Diameter Field Eyepiece (mm): 1.8
Operating Temperature (°C): -5 to +45
Operating Humidity: 20 - 80%
Working Distance (mm): 20.0
Weight (g): 310.00
Note: Example Application: passivation (insulation films) of semiconductor circuits and repair of color filters of LCD panels (defect repair)
Style: Infinity Corrected
Manufacturer: Mitutoyo
Parfocal Length (mm): 95
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)