

TECHSPEC®

1:1 with 25mm and 25mm EFL Achromats, 15mm Achromatic Pair



TECHSPEC Mounted Achromatic Lens Pairs

Stock #55-271

10 TO 12 DAYS



1



₹15,878.00

ADD TO CART

Qty 1-5

₹15,878.00

Qty 6+

₹12,702.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
9.5

Center Air Spacing (mm):
2.20

Substrate:

[N-BAF10](#) / [N-SF10](#) / [N-BAF10](#) / [N-SF10](#)

Surface Quality:

40-20
Working f#: f/2.63
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Effective Focal Length EFL A (mm): 25.00
Effective Focal Length EFL B (mm): 25.00
Housing Diameter (mm): 15 +0.0/-0.10
Housing Length (mm): 21 ±0.2
Lens Edge Spacing at Mount (mm): 4
Magnification: 1:1
Object Distance (mm): 18.05
Image Distance (mm): 18.05
Construction: Achromat Pair in Anodized Aluminum Housing
Type: Relay Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View