

TECHSPEC<sup>®</sup> 11.2mm CA, 20mm FL, Mounted MgF<sub>2</sub> Coated Plano-Convex Lens



Mounted MgF<sub>2</sub> Coated Plano-Convex (PCX) Lenses



Stock #12-916 CLEARANCE 10 TO 12 DAYS

- 1 +

₹3,737.00

ADD TO CART

Qty 1+

₹3,737.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Effective Focal Length EFL (mm):  
20.00

Substrate: ☐  
[N-BK7](#)

f/#:  
1.67

|                                                                         |
|-------------------------------------------------------------------------|
| <b>Numerical Aperture NA:</b><br>0.30                                   |
| <b>Coating:</b><br>MgF <sub>2</sub> (400-700nm)                         |
| <b>Type:</b><br>Plano-Convex Lens                                       |
| <b>Wavelength Range (nm):</b><br>400 - 700                              |
| <b>Back Focal Length BFL from Housing (mm):</b><br>17.69                |
| <b>Bevel:</b><br>Protective bevel as needed                             |
| <b>Clear Aperture CA (mm):</b><br>11.2                                  |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤ 1.75% @ 400 - 700nm |
| <b>Edge Thickness ET (mm):</b><br>1.58                                  |
| <b>Focal Length Specification Wavelength (nm):</b><br>587.6             |
| <b>Focal Length Tolerance (%):</b><br>±1                                |
| <b>Radius R<sub>1</sub> (mm):</b><br>10.34                              |
| <b>Surface Quality:</b><br>40-20                                        |
| <b>Lens Included:</b><br><a href="#">#49-887</a>                        |
| <b>Mount Included:</b><br><a href="#">#54-615</a>                       |
| <b>Mount Diameter (mm):</b><br>30.0                                     |
| <b>Extension Length (mm):</b><br>5.6                                    |
| <b>Total Length (mm):</b><br>9.6                                        |
| <b>Thread Type:</b><br>C-Mount                                          |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                   |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                             |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |