

TECHSPEC® 1150nm 50mm Diameter, OD 2.0 Shortpass Filter



TECHSPEC OD 2.0 Shortpass Filters

Stock **#67-291** CLEARANCE 10 TO 12 DAYS

- 1 + **₹17,661.00**

ADD TO CART

Qty 1+

₹17,661.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-Off Wavelength (nm):
1,150.00

Substrate:

Fused Silica (Coming 7980)	
Coating:	Traditional Coated
Rejection Wavelength (nm):	1240 - 1510
Surface Quality:	40-20
Thickness (mm):	5.00
Thickness Tolerance (mm):	±0.1
Transmission (%):	>85
Transmission Wavelength (nm):	525 - 1100
Type:	Shortpass Filter
Clear Aperture (%):	80.00
Transmitted Wavefront, P-V:	λ/4
Slope Factor (%):	±3
Cut-Off Tolerance (%):	±2
Wavelength Range (nm):	525 - 1510

Regulatory Compliance

RoHS 2015:	Compliant
Reach 224:	Compliant
Certificate of Conformance:	View