

300 x 300mm, 0.16mm FL, Lenticular Array



Stock **#22-727** CLEARANCE CONTACT US

- 1 + **₹16,264.65**

ADD TO CART

Qty 1+
₹16,264.65

Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
0.16

Substrate: ☐
Acrylic

Coating:
Uncoated

Type:
Lens Array

Wavelength Range (nm):
400 - 1600

Center Thickness CT (mm): 2.00
Dimensional Tolerance (mm): ±0.5
Dimensions (inches): 11.811 x 11.811
Dimensions (mm): 300 x 300
Effective Focal Length EFL (inches): 0.006
Effective Size (inches): 11.811 x 11.811
Index of Refraction n_d: 1.49
Note: Warpage Tolerance of ±3mm
Number of Lenses: 212 per 25.4mm
Operating Temperature (°C): 60 (Maximum)
Thickness Tolerance (mm): ±0.1
Effective Size (mm): 300 x 300

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View