

1.2 OD M34 x 0.50, Machine Vision Absorptive ND Filter



Stock #21-719 10 TO 12 DAYS



1



₹5,438.00

ADD TO CART

Qty 1-9

₹5,438.00

Qty 10+

₹5,203.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Optical Density OD (Average):
1.2

Clear Aperture CA (mm):
29.00

Filter Thread:
M34 x 0.50

Substrate: ☐
ND Filter Glass

Surface Quality: 40-20
Transmission (%): 6.25
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
