

1200 Grooves/mm, 12.5 x 25mm, VIS Holographic Grating



Reflective Holographic Gratings

Stock **#43-215** 10 TO 12 DAYS

-

1

+

₹11,397.00

ADD TO CART

Qty 1+
₹11,397.00
Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm):
1200

Wavelength Range (nm):
400 - 700

Dimensions (mm):
12.5 x 25.0 ±0.5

Coating:
Bare Aluminum

Construction: Holographic Grating
Length (mm): 25.00
Substrate:  Float Glass
Thickness (mm): 9.50 ±0.5
Type: Reflective Diffraction Grating
Wavelength: VIS
Width (mm): 12.50
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%): 73
Peak Efficiency Avg, Typical (%): >63

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
