

# Richardson Gratings™ 1200 Grooves, 25 x 25mm, 750nm, Plane Ruled Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock #37-137 10 TO 12 DAYS



1



₹14,616.00

ADD TO CART

Qty 1+

₹14,616.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Groove Density (grooves/mm):  
1200

Wavelength Range (nm):  
450 - 1500

Blaze Wavelength (nm):  
750 ±25

|                                                           |
|-----------------------------------------------------------|
| <b>Blaze Angle (°):</b><br>26.7                           |
| <b>Peak Efficiency, Typical (%):</b><br>91                |
| <b>Dimensions (mm):</b><br>25.0 x 25.0 ±0.1               |
| <b>Clear Aperture (%):</b><br>>90                         |
| <b>Coating:</b><br>Aluminium                              |
| <b>Construction:</b><br>Ruled Grating                     |
| <b>Length (mm):</b><br>25.00                              |
| <b>Substrate:</b> <input type="checkbox"/><br>Float Glass |
| <b>Thickness (mm):</b><br>6.00 ±0.5                       |
| <b>Type:</b><br>Reflective Diffraction Grating            |
| <b>Width (mm):</b><br>25.00                               |
| <b>Reflected Wavefront, RMS:</b><br>λ/4                   |
| <b>Centering of Ruled Area on Substrate (mm):</b><br>±1   |
| <b>Alignment of Grooves to Edge (°):</b><br>±0.15         |
| <b>Groove Spacing Tolerance (%):</b><br><0.05             |
| <b>Polarization:</b><br>S and P                           |
| <b>Master Reference:</b><br>2917                          |
| <b>Spectral Order (m):</b><br>1                           |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br>Compliant                                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |