

TECHSPEC[®] 12.0mm Dia. x -18 FL, YAG-BBAR, Plano-Concave Lens



Stock #21-312 10 TO 12 DAYS

-

1

+

₹3,872.00

ADD TO CART

Qty 1-9	₹3,872.00
Qty 10+	₹3,480.00
Volume Pricing	Request Quote

Get Product Downloads



Diameter (mm):
12.00

Effective Focal Length EFL (mm):
-18.00

Substrate: N-SF11
f/#: 1.00
Numerical Aperture NA: 0.33
Coating: YAG-BBAR (500-1100nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 500 - 1100
Back Focal Length BFL (mm): -19.95
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50 ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 11.00
Coating Specification: R_{abs} <0.25% @ 532nm R_{abs} <0.25% @ 1064nm R_{avg} <1.0% @ 500 - 1100nm
Edge Thickness ET (mm): 4.70
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -14.12
Surface Quality: 40-20
Damage Threshold, By Design: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant