


TECHSPEC® 12.0mm Dia. x -30 FL, Uncoated, UV Plano-Concave Lens



UV Fused Silica Plano-Concave (PCV) Lenses



Stock **#48-047** 10 TO 12 DAYS

[Other Coating Options](#)

- 1 +

₹10,527.00

ADD TO CART

Qty 1-5
₹10,527.00
Qty 6+
₹8,417.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-30.00
Substrate: Fused Silica (Corning 7980)
f#: 2.5
Numerical Aperture NA: 0.20
Coating: Uncoated
Type: Plano-Concave Lens
Wavelength Range (nm): 200 - 2200
Back Focal Length BFL (mm): -31.37
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 11
Edge Thickness ET (mm): 3.24
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Note: Max. Flat Annulus is 0.3mm
Radius R₁ (mm): -13.75
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View