

TECHSPEC®

12.0mm Diameter x -12 FL, MgF₂ Coated, Plano-Concave Lens



Stock **#45-015**

10 TO 12 DAYS

[Other Coating Options](#)

-

1

+

₹3,089.00

ADD TO CART

Qty 1-9
₹3,089.00
Qty 10+
₹2,784.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):

12.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-12.00

Substrate: N-SF11
f/#: 1.00
Numerical Aperture NA: 0.50
Coating: MgF₂ (400-700nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): -13.23
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.20
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 11.00
Coating Specification: R_{avg} ≤1.75% @ 400 - 700nm
Edge Thickness ET (mm): 4.12
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -9.42
Surface Quality: 40-20
Damage Threshold, By Design: 10 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View