

TECHSPEC® 12.5" Diameter x 125" FL Uncoated, Parabolic Mirror



Stock #35-730-000 10 TO 12 DAYS

- 1 +

₹249,255.00

ADD TO CART

Qty 1-2
₹249,255.00
Qty 3+
₹211,845.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate: 

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 12.5 +0.06/-0
Diameter (mm): 317.50 +1.5/-0
Effective Focal Length EFL (inches): 125.0
Effective Focal Length EFL (mm): 3,175.00
Radius of Curvature (mm): 6,350.00
Aperture (f/#): f/10
Coating: Uncoated
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 286
Edge Thickness ET (inches): 2.13
Edge Thickness ET (mm): 54.10
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View