

[See all 7 Products in Family](#)

1.25", White, High Intensity Pattern Projecting Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination High Intensity Pattern Projecting Spot Lights

Stock **#18-638** **1 In Stock**

⊖ 1 ⊕ ₹91,350

ADD TO CART

Volume Pricing	
Qty 1+	₹91,350 each
Need More?	Request Quote

Product Downloads

General

SL256-WHIC **Model Number:**

50000 **LED Lifetime (hours):**

LED Illuminator **Type of Illumination:**

Note:
Optional Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are Available

Advanced Illumination **Manufacturer:**

Spot Light **Geometry:**

Constant **Illumination Mode:**

Physical & Mechanical Properties

1.25 **Diameter (inches):**

413 **Weight (g):**

20.8 **Diameter of Compatible Reticle (mm):**

Optical Properties

White **Color:**

Electrical

0.794 **Minimum Input Current:**

Hardware & Interface Connectivity

Flying Leads **Connector:**

Power Supply:
Power Supply Required and Sold Separately.
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#66-855](#)

2 **Length of Cable (m):**

Environmental & Durability Factors

0 - 50 **Operating Temperature (°C):**

IP50 **Environmental Rating:**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **Reach 233:**

United States **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

Product Details

- Intense Output up to 2,000 Lux
- Includes Heat Sink for Thermal Management
- Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended
- Compatible [Reticles](#) Also Available

Advanced Illumination High Intensity Pattern Projecting Spot Lights offer clusters of high intensity LEDs up to 2,000 lux for focused, homogenous illumination. The spot lights are constructed with a large heat sink, improving thermal management to facilitate increased brightness while maintaining safe operating temperatures. For ease of integration, these LED light projectors are compatible with our [full selection of 21mm diameter reticles](#), including crosshair, concentric circles, and net grid. Advanced Illumination High Intensity Pattern Projecting Spot Lights are compatible with 2/3" format C-Mount lenses and are ideal for machine vision inspection applications, such as edge detection, locating offsets, and assessing topography.

Note: Requires 24V power supply [#66-855](#). Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are recommended and sold separately.