

12.5 x 12.5mm UV Fused Silica Ground Glass Optical Diffuser



Stock **#63-225** 20+ In Stock

-

1

+

₹3,888

ADD TO CART

Volume Pricing	
Qty 1-10	₹3,888 each
Qty 11-49	₹3,081 each
Need More?	Request Quote

Product Downloads

General

Type:

Ground Glass Diffuser

Physical & Mechanical Properties

Dimensions (mm):

12.50 x 12.50

Grit:

220

Thickness (mm):

1.60


12.50	Width (mm):
12.50	Length (mm):
Optical Properties	
Fused Silica (Corning 7980)	Substrate: ☐
200 - 2200	Wavelength Range (nm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Even, Diffuse Surface
- Ideal for Applications Utilizing UV Wavelengths
- Low Scatter Loss
- [Float Glass Substrates](#) Also Available

UV Fused Silica Ground Glass Diffusers are comprised of high tolerance, quality ground glass, making them ideal for a variety of industrial applications. A 220-grit sandblast is used to create a diffuse surface on the UV fused silica substrate of these optical diffusers. Undergoing two orthogonal passes during this sandblast process yields an even diffusion across the surface. The scattering is a compromise of low scatter loss and medium diffusion. UV Fused Silica Ground Glass Diffusers are typically applied for use in screens, illuminator diffusion, and targets.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts