

# 317.5mm/12.5" Optic Dia., Optical Cell Kinematic Mount



Stock #36-480 10 TO 12 DAYS

- 1 + **₹501,642.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-4                       |
| ₹501,642.00                   |
| Qty 5+                        |
| ₹442,404.00                   |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

|                                          |
|------------------------------------------|
| Type:<br>Adjustable - Tip-Tilt           |
| Type of Optics:<br>Circular              |
| Size of Compatible Optics (mm):<br>317.5 |

|                                                                  |
|------------------------------------------------------------------|
| <b>Clear Aperture CA (inches):</b><br>12.08                      |
| <b>Clear Aperture CA (mm):</b><br>306.8                          |
| <b>Optical Centerline (mm):</b><br>203.2                         |
| <b>Range:</b><br>7°                                              |
| <b>Dimensions (inches):</b><br>16.00 x 8.00 x 15.00              |
| <b>Dimensions (mm):</b><br>406.4 x 203.2 x 381.0                 |
| <b>Weight (lbs):</b><br>41.0                                     |
| <b>Inner Diameter (inches):</b><br>12.56                         |
| <b>Construction:</b><br>Black Anodized Aluminum, Stainless Steel |
| <b>Diameter of Compatible Optics (inches):</b><br>12.50          |
| <b>Optical Centerline (inches):</b><br>8.00                      |
| <b>Optic Holding Style:</b><br>Three Spring-Loaded Clips         |
| <b>Max. Thickness of Compatible Optics (mm):</b><br>53.0         |
| <b>Adjustment Screw Pitch (inches):</b><br>0.031                 |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |