

TECHSPEC® 12.5mm, 785 V-Coat, N-BK7 Laser Line RA Prism



Stock **#83-222** CLEARANCE 10 TO 12 DAYS

- 1 + **₹2,953.65**

ADD TO CART

Qty 1+
₹2,953.65

Volume Pricing
Request Quote

Get Product Downloads



Angle Tolerance (arcsec):
±15

Coating:
Laser V-Coat (785nm)

Design Wavelength DWL (nm):
785

Substrate: ☐
[N-BK7](#)

Surface Quality:
40-20

Type: Right Angle Prism
Dimensional Tolerance (mm): +0.00/-0.10
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 17.70
Length of Legs (mm): 12.50
Image Orientation: Left-Handed
Coating Specification: R _{abs} <0.25% @ 785nm
Ray Deviation (°): 90
Surface Flatness (P-V): λ/8

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View