

TECHSPEC® 125mm, Center Drive, Thru-Hole, English Stage



TECHSPEC® Crossed-Roller Bearing Linear Translation Stages (Thru-Hole Model)



Stock **#66-462** 10 TO 12 DAYS

- 1 +

₹51,156.00

ADD TO CART

Qty 1-2

₹51,156.00

Qty 3+

₹44,622.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:

Lead Screw
Drive Orientation: Center Drive
Type: English
Stage Size (mm): 125 x 125
Travel (inches): 1
Center Hole: M42 x 0.75
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 20
Mounting Threads: (1) M42 x 0.75, (20) 1/4-20
Stage Size (inches): 4.92 x 4.92
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant