

TECHSPEC® 12.5mm Dia, 0.50 Numerical Aperture Uncoated, Aspheric Lens



Stock **#69-855** 10 TO 12 DAYS

[Other Coating Options](#)

− 1 +

₹16,965.00

ADD TO CART

Qty 1-5
₹16,965.00
Qty 6+
₹13,572.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.1

Effective Focal Length EFL (mm):
12.50 @ 587.6nm

Numerical Aperture NA:
0.50

Back Focal Length BFL (mm): 9.35
Substrate: L-BAL35
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 11.25
Edge Thickness ET (mm): 2.11
Center Thickness CT (mm): 5.00 ±0.1
f#: 1.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 330 - 2400
Conjugate Distance: Infinite
Power (diopters): 80.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View