

TECHSPEC[®] 12.5mm Dia. Enhanced Aluminum, λ/4 Mirror



Stock #45-601 10 TO 12 DAYS

-

1

+

₹4,350.00

ADD TO CART

Qty 1-5
₹4,350.00
Qty 6+
₹3,480.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50

Surface Flatness (P-V):
λ/4

Substrate: ☐
BOROFLOAT[®]

Back Surface:

Commercial Polish
Surface Quality: 60-40
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 2.00 ±0.25
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant