

TECHSPEC® 12.5mm Dia x 12.5mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#46-193** 10 TO 12 DAYS

- 1 + **₹5,394.00**

ADD TO CART

Qty 1-5
₹5,394.00
Qty 6+
₹4,307.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50

Effective Focal Length EFL (mm):
12.50

Substrate:
[N-BK7](#)

f/#:

1
Numerical Aperture NA: 0.5
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 7.57
Center Thickness CT (mm): 7.48
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 2.72
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 6.48
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View