

**TECHSPEC® 12.5mm Dia x 25mm FL Uncoated, Illumination Grade PCX Cylinder Lens**



Stock **#46-194** 10 TO 12 DAYS

- 1 + **₹5,394.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| ₹5,394.00                     |
| Qty 6+                        |
| ₹4,307.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
12.50

Effective Focal Length EFL (mm):  
25.00

Substrate:   
[N-BK7](#)

f/#:

|                                                 |
|-------------------------------------------------|
| <b>Numerical Aperture NA:</b><br>0.25           |
| <b>Coating:</b><br>Uncoated                     |
| <b>Type:</b><br>Cylinder Lens, Plano-Convex     |
| <b>Wavelength Range (nm):</b><br>350 - 2200     |
| <b>Back Focal Length BFL (mm):</b><br>23.09     |
| <b>Center Thickness CT (mm):</b><br>2.90        |
| <b>Center Thickness Tolerance (mm):</b><br>±0.1 |
| <b>Dimensional Tolerance (mm):</b><br>+0.0/-0.2 |
| <b>Edge Thickness ET (mm):</b><br>1.29          |
| <b>Focal Length Tolerance (%):</b><br>±3        |
| <b>Radius R<sub>1</sub> (mm):</b><br>12.96      |
| <b>Surface Quality:</b><br>60-40                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |

---