

12.5mm Diameter, Cyan Dichroic Filter



Additive and Subtractive Dichroic Color Filters

Stock **#52-536** 10 TO 12 DAYS

- 1 + **₹1,914.00**

ADD TO CART

Qty 1-24
₹1,914.00
Qty 25+
₹1,697.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50

Angle of Incidence (°):
0

Cut-Off Wavelength (nm):
590.00

Substrate:  BOROFLOAT®
Operating Temperature (°C): <100
Coating: Subtractive Color
Color: Cyan
Surface Quality: 80-50
Thickness (mm): 2.00 Nominal
Type: Dichroic Filter
Dimensional Tolerance (mm): ±0.25
Clear Aperture (%): ≥85
Coating Specification: T _{avg} >80% @ 400 - 550nm T _{avg} <1.0% @ 640 - 740nm
Cut-Off Wavelength Tolerance (µm): 0.015

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant