

12.5mm Diameter, Optical Cast Plastic Window



Stock #19-824 [CONTACT US](#)

- 1 + MRP ₹2,169

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-49	₹2,169 each
Qty 50-99	₹1,716 each
Qty 100-199	₹1,614 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**
Plastic **Type of Window:**

Physical & Mechanical Properties

0.49 **Diameter (inches):**

12.50 ±0.3	Diameter (mm):
1.50 ±0.15	Thickness (mm):
Optical Properties	
Uncoated	Coating:
Thermoset ADC (CR-39®)	Substrate: <input type="checkbox"/>
1.501	Index of Refraction (n_d):
>90 (typical)	Transmission (%):
59.2	Abbe Number (v_d):
400 - 1500	Wavelength Range (nm):
Material Properties	
1.320	Density (g/cm³):
Environmental & Durability Factors	
100 Continuous, 130 for 1 hour	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Lightweight Alternative to Glass Windows
- Excellent Thermal and Chemical Resistance
- Higher Transmission than Similar Transparent Plastics

Clear Optical Cast Plastic Windows are a lightweight and durable option compared to a glass alternative. These windows have a high transmission and low haze, have 25 - 50 times greater abrasion resistance, and are resistant to all types of chemicals and solvents (acetone, acids, alkali and alcohols). Due to their construction, these windows are able to be drilled using a carbide bit for various mounting needs.

Clear Optical Cast Plastic Windows are uncoated, and are available in circular, rectangular, and square options.

Technical Information

Thermoset ADC (CR-39®)
Typical Transmission

