

12.5mm Diameter, Yellow Dichroic Filter



Additive and Subtractive Dichroic Color Filters

Stock **#52-542** 10 TO 12 DAYS

- 1 + **₹1,914.00**

ADD TO CART

Qty 1-24
₹1,914.00
Qty 25+
₹1,697.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50

Angle of Incidence (°):
0

Cut-On Wavelength (nm):
520.00

Substrate:  BOROFLOAT®

Operating Temperature (°C):
<100

Coating:
Subtractive Color

Color:
Yellow

Surface Quality:
80-50

Thickness (mm):
2.00 Nominal

Type:
Dichroic Filter

Dimensional Tolerance (mm):
±0.25

Clear Aperture (%):
≥85

Cut-On Wavelength Tolerance (µm):
0.015

Coating Specification:
T_{avg} <1.0% @ 400 - 475nm
T_{avg} >80% @ 550 - 750nm

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)