



12.5mm H x 25mm L x -15mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#68-053** 10 TO 12 DAYS

- 1 + **₹5,394.00**

ADD TO CART

Qty 1-5

₹5,394.00

Qty 6+

₹4,307.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Effective Focal Length EFL (mm):
-15.00

Substrate: ☐
[NSF11](#)

Coating:
Uncoated

Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 400 - 2500
Back Focal Length BFL (mm): -16.4
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.5 x 25.0
Edge Thickness ET (mm): 4.11
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -11.77
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View