

125mm Sq. English Kinematic Magnetic Base



Stock **#22-403** **2 In Stock**

-

1

+

₹24,792

ADD TO CART

Volume Pricing	
Qty 1-9	₹24,792 each
Qty 10+	₹22,364 each
Need More?	Request Quote

Product Downloads

General	
English	Type:
The permanent magnet is turned on and off by integrated screw (5mm Hex)	
Note:	
Yes	Switchable:
Physical & Mechanical Properties	
Thickness (mm):	

25.40	
	Width (mm):
125.00	
	Weight (kg):
0.97	
	Construction:
Anodized Aluminum	
	Length (mm):
125.00	
	Repeatability (μrad):
<70.0	

Threading & Mounting

	Mounting Threads:
(71) 1/4-20	

Material Properties

	Magnetic Force (N):
40	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 247:
Compliant	
	Country of Origin:
Taiwan	
	Imported By:
Edmund Optics India Private Limited	

Product Details

- Common 25.4mm (1") Platform Height
- Removable Top Plates with High Repeatability Kinematic Positioning
- Compatible with all with [TECHSPEC Stages](#)

Kinematic Magnetic Base Plates are ideal for simplifying the adjustment of subsystems in a benchtop optical system. The bases feature a common platform height of 25.4mm (1") to allow for simplified optical axis alignment. Each base has a removeable top plate, ideal for adding or removing system components and subassemblies anywhere on a lab table with ease. Internal kinematic positioning allows the top plates to be removed and replaced with high repeatability. Kinematic Magnetic Base Plates are directly compatible with our [TECHSPEC stages](#), making them an ideal lab bench component for system building.