

TECHSPEC<sup>®</sup> 12.5mm Uncoated, Fused Silica High Tolerance RA Prism



TECHSPEC High Tolerance UV Fused Silica Right Angle Prisms

Stock **#47-202** 10 TO 12 DAYS

-

1

+

₹8,700.00

ADD TO CART

Qty 1-5

₹8,700.00

Qty 6+

₹7,830.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle Tolerance (arcsec):  
±40

Coating:  
Uncoated

Substrate: ☐  
[Fused Silica](#) (Coming 7980)

|                                                 |
|-------------------------------------------------|
| <b>Surface Quality:</b><br>20-10                |
| <b>Type:</b><br>Right Angle Prism               |
| <b>Dimensional Tolerance (mm):</b><br>+0.0/-0.1 |
| <b>Bevel:</b><br>Protective bevel as needed     |
| <b>Length of Hypotenuse (mm):</b><br>17.70      |
| <b>Length of Legs (mm):</b><br>12.50            |
| <b>Pyramid Tolerance (arcmin):</b><br>±1        |
| <b>Image Orientation:</b><br>Left-Handed        |
| <b>Wavelength Range (nm):</b><br>200 - 2200     |
| <b>Surface Flatness (P-V):</b><br>λ/10          |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---