

TECHSPEC® 12.5mm, Uncoated, Fused Silica, Right Angle Prism



TECHSPEC UV Fused Silica Right Angle Prisms

Stock **#47-784** 10 TO 12 DAYS

- 1 + **₹7,395.00**

ADD TO CART

Qty 1-5
₹7,395.00
Qty 6+
₹5,916.00
Volume Pricing
Request Quote

Get Product Downloads



Coating:
Uncoated

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Surface Quality:
60-40

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.10 Legs
Angle Tolerance (arcmin): ±5
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 17.70
Length of Legs (mm): 12.50
Pyramid Tolerance (arcmin): ±5
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): λ/2

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View