

TECHSPEC[®] S-Mount, 12.5mm x 17.6mm Plate Mount



Plate S-Mount Holder (#11-142)

Stock **#11-142** 2 In Stock

-

1

+

₹18,484

ADD TO CART

Volume Pricing	
Qty 1-4	₹18,484 each
Qty 5-9	₹17,281 each
Qty 10-25	₹16,438 each
Need More?	Request Quote

Product Downloads

General	
Optic Mount (Fixed)	Function:
Rectangular	Type of Optics:
Includes one S-Mount Aperture Cap (# 11-137)	
Note:	
Dimensions of Compatible Optics (mm):	
12.5 x 17.6	

Physical & Mechanical Properties	
30.0 x 30.0 x 28.5	Dimensions (mm):
30.0	Extension Length (mm):
1.0	Min. Thickness of Compatible Optics (mm):
3.0	Max. Thickness of Compatible Optics (mm):
Threading & Mounting	
S-Mount	Thread Type:
1/4-20	Compatible Post:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- 1/4-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: #11-139 and #11-142 each include one S-Mount Aperture Cap (#11-137)

Technical Information

