

127mm Clear Aperture, 30 Arcsec, Aluminum Retroreflector



Stock #49-673 CLEARANCE 10 TO 12 DAYS

- 1 +

₹235,335.00

ADD TO CART

Qty 1+
₹235,335.00

Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcsec): 30.00
Clear Aperture CA (mm): 127.0
Coating: Enhanced Aluminum (450-650nm)
Diameter (mm): 166.70
Exiting Wavefront Accuracy: 18.0λ

Substrate:  BOROFLOAT®

Surface Quality:
80-50

Mounting Threads:
(7) ¼-20, (6) M6 x 1.0

Type:
Retroreflector

Dimensional Tolerance (mm):
±1.6

Image Orientation:
Left-Handed

Ray Deviation (°):
180

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS 2015:
[Compliant](#)

REACH 201:
[Compliant](#)

Certificate of Conformance:
[View](#)