

[See all 39 Products in Family](#)

**TECHSPEC® 12.7mm Dia.  $\lambda/10$  ZERODUR® Optical Flat**



Stock #43-327-000 **20+ In Stock**

MRP ₹10,594

● Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | ₹10,594 each                  |
| Qty 11-25      | ₹9,383 each                   |
| Qty 26-49      | ₹8,878 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Interferometry Window **Type:**

**Physical & Mechanical Properties**

11.40 **Clear Aperture CA (mm):**

|                      |  |
|----------------------|--|
| 0.50 +0.00/-0.02     | <b>Diameter (inches):</b>                  |
| 12.70 +0.0/-0.50     | <b>Diameter (mm):</b>                      |
| 0.13 ±0.03           | <b>Thickness (inches):</b>                 |
| 3.20 ±0.8            | <b>Thickness (mm):</b>                     |
| ≤3                   | <b>Parallelism (arcmin):</b>               |
| Protective as needed | <b>Bevel:</b>                              |
| Single Surface       | <b>Construction:</b>                       |
| Fine Ground          | <b>Edges:</b>                              |
| 0.24                 | <b>Poisson's Ratio:</b>                    |
| 90.3                 | <b>Young's Modulus (GPa):</b>              |
| 620.00               | <b>Knoop Hardness (kg/mm<sup>2</sup>):</b> |

## Optical Properties

|             |   |
|-------------|---|
| Uncoated    | <b>Coating:</b>                             |
| Yellow Tint | <b>Color:</b>                               |
| ZERODUR®    | <b>Substrate:</b> <input type="checkbox"/>  |
| 1.542       | <b>Index of Refraction (n<sub>d</sub>):</b> |
| 60-40       | <b>Surface Quality:</b>                     |
| 56.2        | <b>Abbe Number (v<sub>d</sub>):</b>         |
| λ/10        | <b>Surface Flatness (P-V):</b>              |

## Material Properties

|      |   |
|------|---|
| 2.53 | <b>Density (g/cm<sup>3</sup>):</b>                                |
| 0.1  | <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b> |

## Regulatory Compliance

|   |                                    |
|---|------------------------------------|
| Compliant   | <b>RoHS 2015:</b>                  |
| View  | <b>Certificate of Conformance:</b> |
| Compliant   | <b>Reach 240:</b>                  |
| China   | <b>Country of Origin:</b>          |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 | <b>Imported By:</b>                |

## Product Details

- Sizes Ranging from ½" Diameter to 14" Diameter
- Each λ/20 Flat 76.2mm and Larger Includes a Certificate of Calibration
- Available with Standard Metallic Mirror Coatings: [λ/10 and λ/20 Mirrors](#)

TECHSPEC® Single Surface Optical Flats are used as a reference (test plate) against which the flatness of an unknown surface may be compared. Each piece is precision polished by our master opticians and tested on a Zygo interferometer to insure the surface flatness. The secondary surfaces of our single surface flats are pitch polished to window quality for viewing the interference pattern. TECHSPEC Single Surface Optical Flats ship in a durable storage case for permanent protection. λ/20 flats that are 76.2mm or larger also include a certificate of calibration.