

TECHSPEC<sup>®</sup> 12.7mm Dia., Uncoated, Ultrafast Thin Window



Stock #11-749 10 TO 12 DAYS

-

1

+

₹8,265.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| ₹8,265.00                     |
| Qty 6+                        |
| ₹7,439.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Coating:  
Uncoated

Diameter (mm):  
12.70 +0.00/-0.10

Substrate: 

Fused Silica (Corning 7980)

Index of Refraction n<sub>d</sub>:

|                                             |
|---------------------------------------------|
| 1.458                                       |
| <b>Surface Quality:</b><br>20-10            |
| <b>Thickness (mm):</b><br>1.00 ±0.10        |
| <b>Type:</b><br>Ultrafast Window            |
| <b>Bevel:</b><br>Protective as needed       |
| <b>Clear Aperture (%)</b> :<br>90           |
| <b>Transmitted Wavefront, P-V:</b><br>λ/6   |
| <b>Abbe Number (v<sub>d</sub>):</b><br>67.8 |
| <b>Parallelism (arcsec):</b><br>≤30         |
| <b>Wavelength Range (nm):</b><br>200 - 2200 |
| <b>Fused Silica Grade:</b><br>7979 0G       |
| <b>Edges:</b><br>Fine Ground                |
| <b>Type of Window:</b><br>Glass             |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |