

TECHSPEC[®] 12.7mm Dia. x 25mm FL, Uncoated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCX Lenses

Stock #38-634 10 TO 12 DAYS

[Other Coating Options](#)

-

1

+

₹12,615.00

ADD TO CART

Qty 1-5

₹12,615.00

Qty 6+

₹10,092.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.70 +0.00/-0.025

Effective Focal Length EFL (mm):
25.00 @ 355nm

Back Focal Length BFL (mm):
21.62

Coating: Uncoated
Substrate: Fused Silica (Coming 7980)
Surface Quality: 10-5
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: $\lambda/10$
Focal Length Tolerance (%): ± 1
Centering (arcmin): <1
Center Thickness CT (mm): 5.00 $\pm$ 0.10
Edge Thickness ET (mm): 3.16
Radius R₁ (mm): 11.90
Clear Aperture CA (mm): 11.43
f#: 1.97
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View