

TECHSPEC[®] 12.7mm Dia. x 50.8mm FL, Uncoated, Plano-Convex Lens



Stock **#49-846** 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹2,436.00

ADD TO CART

Qty 1-9
₹2,436.00
Qty 10+
₹2,197.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.70 +0.0/-0.025

Effective Focal Length EFL (mm):
50.80 @ 587.6nm

Back Focal Length BFL (mm): 49.15
Coating: Uncoated
Substrate:  N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.50 ±0.10
Edge Thickness ET (mm): 1.72
Radius R₁ (mm): 26.25
Clear Aperture CA (mm): 11.7
f#: 4
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View