

[See all 12 Products in Family](#)

**TECHSPEC® 12.7mm Dia., 2mm Thick, Uncoated, Magnesium Fluoride Window**



Magnesium Fluoride (MgF<sub>2</sub>) Windows

Stock #17-281 **9 In Stock**

1 MRP ₹23,508

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹23,508 each
Qty 11-25	₹20,683 each
Qty 26-49	₹19,472 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Protective Window **Type:**

Crystal **Type of Window:**

**Physical & Mechanical Properties**

Clear Aperture CA (mm):

11.43	<b>Diameter (mm):</b>
12.70 +0.0/-0.1	
	<b>Thickness (mm):</b>
2.00 ±0.1	
	<b>Parallelism (arcmin):</b>
<1	
	<b>Bevel:</b>
Protective as needed	
	<b>Clear Aperture (%):</b>
90	
	<b>Edges:</b>
Fine Ground	
	<b>Poisson's Ratio:</b>
0.27	
	<b>Young's Modulus (GPa):</b>
138	
	<b>Knoop Hardness (kg/mm<sup>2</sup>):</b>
415.00	

## Optical Properties

	<b>Coating:</b>
Uncoated	
	<b>Substrate:</b> <input type="checkbox"/>
Magnesium Fluoride (MgF <sub>2</sub> )	
	<b>Index of Refraction (n<sub>d</sub>):</b>
1.377	
	<b>Surface Quality:</b>
40-20	
	<b>Abbe Number (v<sub>d</sub>):</b>
106.22	
	<b>Wavelength Range (nm):</b>
120 - 7000	
	<b>Surface Flatness (P-V):</b>
λ/2	

## Material Properties

	<b>Density (g/cm<sup>3</sup>):</b>
3.18	
	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>
13.7	

## Regulatory Compliance

	<b>Certificate of Conformance:</b>
<a href="#">View</a>	
	<b>Country of Origin:</b>
United States	
	<b>Imported By:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Excellent Transmission from 120nm to 7μm
- Rugged and Durable
- Resistant to Chemical Etching

TECHSPEC® Magnesium Fluoride (MgF<sub>2</sub>) Windows offer excellent broadband transmission from the deep-UV to the mid-infrared. DUV transmission makes them ideal for use at the Hydrogen Lyman-alpha line and for UV radiation sources and receivers, as well as excimer laser applications. MgF<sub>2</sub> is a rugged material resistant to chemical etching, laser damage, and mechanical and thermal shock. TECHSPEC® Magnesium Fluoride (MgF<sub>2</sub>) Windows have a Knoop Hardness of 415 and index of refraction of 1.38. The windows are offered in diameters ranging from 5 to 75mm.

## Technical Information

