

TECHSPEC® 12.7mm H x 12.7mm L x 100mm FL VIS 0°, Illumination Grade PCX Cylinder Lens



Stock **#36-210** 10 TO 12 DAYS

-

1

+

₹7,134.00

ADD TO CART

Qty 1-5
₹7,134.00
Qty 6+
₹5,699.00
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
100.00

Substrate: N-BK7

f/#:
7.8740157480315

Numerical Aperture NA:

0.06
Coating: MS 0° (425-675nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): 98.02
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.7 x 12.7
Edge Thickness ET (mm): 2.61
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 51.68
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant