

TECHSPEC®

12.7mm H x 12.7mm L x 25mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #35-021 10 TO 12 DAYS

- 1 + ₹5,394.00

ADD TO CART

Qty 1-5
₹5,394.00
Qty 6+
₹4,307.00
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
25.00

Substrate: ☐
[N-BK7](#)

f/#:
1.96850393700787

Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 23.02
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.7 x 12.7
Edge Thickness ET (mm): 1.33
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 12.92
Surface Quality: 60-40

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View