

TECHSPEC® 12.7mm Silver and VIS 0° Coated, Mounted Corner Cube Retroreflector



Mounted N-BK7 Corner Cube Retroreflectors



Stock **#12-216** 10 TO 12 DAYS

- 1 +

₹31,755.00

ADD TO CART

Qty 1-5
₹31,755.00
Qty 6+
₹25,404.00
Volume Pricing
Request Quote

Get Product Downloads



Beam Deviation (arcsec):
±5

Coating:
VIS 0° & Silver with protective overcoat

Diameter Tolerance (mm): +0.0/-0.1
Substrate: N-BK7
Inner Diameter (mm): 12.70
Outer Diameter (mm): 31.75
Surface Quality: 60-40
Mounting Threads: (2) 1/4-20 Tapped Holes
Type: Retroreflector
Housing Tolerance (mm): Outer Diameter: +0/-0.5, Height:± 0.25
Image Orientation: Left-Handed
Coating Specification: Reflective Surfaces: R_{abs} > 97% FROM400 - 2500nm @ 0° AOI R_{avg} > 98% FROM400 - 2500nm @ 0° AOI Entrance: R_{avg} ≤0.4% @ 425 - 675nm
Ray Deviation (°): 180
Wavelength Range (nm): 425 - 675
Surface Flatness (P-V): λ/8
Power (fringes) @ 632.8nm: 0.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View