

TECHSPEC[®] 12.7mm Uncoated, Littrow Dispersion Prism



30° - 60° - 90° Littrow Dispersion Prisms

Stock #43-648 10 TO 12 DAYS



1



₹5,438.00

ADD TO CART

Qty 1-5

₹5,438.00

Qty 6+

₹4,350.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Coating:

Uncoated

Substrate: ☐

[N-BK7](#)

Length (mm):

12.70

Surface Quality:

80-50
Type: Littrow Prism
Dimensional Tolerance (mm): ±0.13
Angle Tolerance (arcmin): ±10
Bevel: Protective bevel as needed
Image Orientation: Right-Handed
Ray Deviation (°): 60
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): 1λ @ 632.8nm

Regulatory Compliance

RoHS: Compliant
REACH 201: Compliant
Certificate of Conformance: View