

TECHSPEC® 12.7mm x -50mm FL, Uncoated Imaging Grade PCV Cylinder Lens



TECHSPEC® Beam Shaping PCV Cylinder Lenses

Stock **#34-619** 10 TO 12 DAYS

- 1 + **₹6,873.00**

ADD TO CART

Qty 1-5
₹6,873.00
Qty 6+
₹5,481.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.70 +0.0/-0.025

Effective Focal Length EFL (mm):
-50.00

Substrate: ☐
[N-BK7](#)

f/#: 4
Numerical Aperture NA: 0.13
Coating: Uncoated
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -51.32
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 11.43
Edge Thickness ET (mm): 2.74
Radius R₁ (mm): 25.84
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <5
Power Axis Wedge (arcmin): <5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View