

128mm Dia x 288mm FL Alum. Coated, Ellipsoidal Reflector



Precision Ellipsoidal Reflectors

Stock #90-970 [CONTACT US](#)

- 1 + **₹40,803.00**

ADD TO CART

Qty 1-10
₹40,803.00
Qty 11+
₹35,801.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate: [BOROFLOAT®](#)

Coating:
Protected Aluminum (400-700nm)

Coating Specification:
Ravg >85% @400 - 700nm

Coating Type:

Metal
Center Hole Diameter (mm): 31.0
Height (mm): 67.7
Inner Diameter (mm): 121
Outer Diameter (mm): 128.00 +0.0/-0.5
Type: Specialty Mirror
Wavelength Range (nm): 400 - 700
Distance to Focal Point f_1 (mm) : 17.8
Distance to Focal Point f_2 (mm): 294

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View