

[See all 4 Products in Family](#)

12mm Dia. x 48mm FL, Commercial Grade, Plano-Convex Lens



Stock #23-074 **CLEARANCE** 15 In Stock

[Other Coating Options](#)

1 MRP ₹2,069

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,069 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens **Type:**

Physical & Mechanical Properties

12.00 +0.00/-0.10 **Diameter (mm):**

6.00 **Centering (arcmin):**

Center Thickness CT (mm):

2.00

Edge Thickness ET (mm):

1.26

Clear Aperture CA (mm):

≥10.2

Optical Properties

Effective Focal Length EFL (mm):

48.00

Back Focal Length BFL (mm):

46.69

Coating:

Uncoated

Substrate: □

N-BK7

Focal Length Tolerance (%):

±1

Radius R₁ (mm):

24.81

f#:

4.00

Numerical Aperture NA:

0.13

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

China

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Feature Standard Designs and Specifications
- Also Available with [MgF₂ Coating](#)
- For More Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. Commercial Grade Uncoated Plano-Convex(PCX) Lenses offer commercial quality, at an affordable price.

Technical Information

