

12mm Dia x -7.75mm FL Enhanced Aluminum Coated, Convex Mirror



Stock #64-056 10 TO 12 DAYS

- 1 + **₹3,480.00**

ADD TO CART

Qty 1-5
₹3,480.00
Qty 6+
₹3,132.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
12.00 +0.00/-0.10

Focal Length FL (mm):
-7.75

Center Thickness CT (mm):
3.00

Clear Aperture (%):
90

Coating: Enhanced Aluminum (450-650nm)
Coating Specification: R_{avg} >95% @450 - 650nm
Coating Type: Metal
Edge Thickness ET (mm): 1.79
Focal Length Tolerance (%): ±2
Radius R (mm): 15.50
Substrate: N-BK7
Surface Quality: 60-40
Type: Spherical Mirror
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: 0.2 J/cm² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant