

TECHSPEC®

12mm Diameter x -12 FL, VIS 0° Coated, Plano-Concave Lens



Stock **#47-905**

CONTACT US

Other Coating Options

-

1

+

₹3,654.00

ADD TO CART

Qty 1-9

₹3,654.00

Qty 10+

₹3,284.00

Volume Pricing

Request Quote

Get Product Downloads



Diameter (mm):

12.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-12.00

Substrate: N-SF11
f/#: 1.00
Numerical Aperture NA: 0.50
Coating: VS 0° (425-675nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): -13.23
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.20
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 11.00
Coating Specification: R_{avg} ≤0.4% @ 425 - 675nm
Edge Thickness ET (mm): 4.12
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -9.42
Surface Quality: 40-20
Damage Threshold, By Design: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant