

TECHSPEC® 12mm EFL Unmounted, RKE Precision Eyepiece



TECHSPEC® RKE® Precision Eyepieces

Stock #66-208 **5 In Stock**

MRP ₹12,309

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-24	₹12,309 each
Qty 25-49	₹9,080 each
Need More?	Request Quote

Product Downloads

General

Type: Unmounted
 Manufacturer: Edmund Optics®

Physical & Mechanical Properties

Eye Relief (mm): 10.70

0.569	Center Air Spacing (mm):
10.43	Total Length, Glass Only (mm):
N/A	Housing Length (mm):
5.768	Image Distance (mm):

Optical Properties

5 (Specified @ 0.7 Field)	Distortion (%):
12.00	Effective Focal Length EFL (mm):
9.7	Field Stop Diameter (mm):
45.00	Apparent Field (°):
5.81	Back Focal Length BFL (mm):
0.016	Lateral Color, 0.7 Field :
4/13 (On-Axis/0.7 Field)	Spot Size (µm):

Regulatory Compliance

View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Full Prescription Data Available
- Long Eye Relief
- Apparent Field of 45°

The RKE® line of eyepieces is one of our most popular designs. Originally produced for telescope use, over time they have proven useful in a wide variety of industrial and medical applications. In addition, to help customers take advantage of the powerful current optical design software, we are pleased to forward full prescription data for these eyepieces.

Prescription information available upon request. Please complete a [Request for Prescription Form](#).

Unmounted RKE Eyepieces include the eye Lens, field Lens, and black anodized spacer between the 2 lenses. Unmounted configurations are designed to provide OEMs with the components required to integrate these eyepieces into customer-designed applications.

Technical Information

