

[See all 5 Products in Family](#)

## 12mm Fixed Focal Length Lens



#86-206

Stock #86-206 [CONTACT US](#)

1  MRP ₹2,29,392

Price inclusive of all taxes

[ADD TO CART](#)

### Volume Pricing

Qty 1+	₹2,29,392 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

**Product Family:**  
4/3" Format Fixed Focal Length Lenses

**Type:**  
Fixed Focal Length Lens

#### Physical & Mechanical Properties

**Iris Option:**  
Variable

**Length (mm):**  
85.00

57.0	<b>Maximum Diameter (mm):</b>
57	<b>Outer Diameter (mm):</b>
270.00	<b>Weight (g):</b>

## Optical Properties

74.9	<b>Horizontal Field of View @ Max Sensor Format:</b>
182.00	<b>Field of View @ Min Working Distance (mm):</b>
21.60	<b>Maximum Image Circle (mm):</b>
12.00	<b>Focal Length FL (mm):</b>
100 - ∞	<b>Working Distance (mm):</b>
f/2 - f/22	<b>Aperture (f#):</b>
<0.6	<b>Distortion (%):</b>
0.59	<b>Maximum Distortion (%):</b>
VS	<b>Lens Wavelength Range:</b>

## Sensor

4/3"	<b>Maximum Sensor Format:</b>
5.00	<b>Pixel Size (µm):</b>

## Threading & Mounting

M55.0 x 0.75	<b>Filter Thread:</b>
C-Mount	<b>Mount:</b>

## Regulatory Compliance

<a href="#">Exempt</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Contains SVHC(s)</a>	<b>REACH 241:</b>
Japan	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Up to 1", C-Mount Lens
- Less than 1.0% TV Distortion
- 12mm to 50mm Focal Length

Available in multiple focal lengths, 4/3" Format Fixed Focal Length Lenses incorporate a floating focus with aspheric lenses to maximize resolution across their entire working distance. Ideal for many machine vision applications, these fixed focal length lenses feature a broadband anti-reflection (AR) coating for maximum transmission. 4/3" Format Fixed Focal Length Lenses are available with focal lengths ranging from 12 - 50mm.