

12mm Fixed Focal Length Lens



#86-206

Stock **#86-206** [CONTACT US](#)

-

1

+

₹1,82,250

ADD TO CART

Volume Pricing	
Qty 1+	₹1,82,250 each
Need More?	Request Quote

Product Downloads

General

4/3" Format Fixed Focal Length Lenses

Series:

Fixed Focal Length Lens

Type:

Physical & Mechanical Properties

Variable

Iris Option:

85.00

Length (mm):

57.0	Maximum Diameter (mm):
57	Outer Diameter (mm):
270.00	Weight (g):
Optical Properties	
74.9	Horizontal Field of View @ Max Sensor Format:
182.00	Field of View @ Min Working Distance (mm):
21.60	Maximum Image Circle (mm):
12.00	Focal Length FL (mm):
100 - ∞	Working Distance (mm):
f/2 - f/22	Aperture (f/#):
<0.6	Distortion (%):
0.59	Maximum Distortion (%):
VS	Lens Wavelength Range:
Sensor	
4/3"	Maximum Sensor Format:
5.00	Pixel Size (µm):
Threading & Mounting	
M55.0 x0.75	Filter Thread:
C-Mount	Mount:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Up to 1", C-Mount Lens
- Less than 1.0% TVDistortion
- 12mm to 50mm Focal Length

Available in multiple focal lengths, 4/3" Format Fixed Focal Length Lenses incorporate a floating focus with aspheric lenses to maximize resolution across their entire working distance. Ideal for many machine vision applications, these fixed focal length lenses feature a broadband anti-reflection (AR) coating for maximum transmission. 4/3" Format Fixed Focal Length Lenses are available with focal lengths ranging from 12 - 50mm.